

Haag-Streit Bern SLIT LAMP MODEL BD900 AND TABLE

The BD 900® is optimised for the optician, optometrist, contact lens practitioners and ophthalmologists specialising in the anterior segment.

SINGAPORE, SINGAPORE, SINGAPORE,
December 11, 2013 /

EINPresswire.com/ -- Haag-Streit Bern SLIT LAMP MODEL BD900 AND TABLE is optimised for the [optician](#), [optometrist](#), contact lens practitioners and ophthalmologists specialising in the anterior segment. It is also ideal for non-ophthalmologists in emergency rooms. Video may be fitted through a built-in video port (C-mount). Standard magnification is 10 and 16x times – through the flip of a lever placed just beneath the microscope.



Maintained key qualities of BM 900 and BQ 900
Integrated video port with C-mount optics
Slit length 14 mm
Yellow filter
Ideal for contact lens fitting

<http://www.tiarantania.com>

“

Haag-Streit Bern SLIT LAMP
MODEL BD900 AND TABLE is
optimised for the optician,
optometrist, contact lens
practitioners and
ophthalmologists
specialising in the anterior
segment”

TIARA INTANIA LTD



AMI YETTI

TIARA INTANIA LTD

627617012867

[email us here](#)

This press release can be viewed online at: <https://www.einpresswire.com/article/180474863>

EIN Presswire's priority is source transparency. We do not allow opaque clients, and our editors try to be careful about weeding out false and misleading content. As a user, if you see something we have missed, please do bring it to our attention. Your help is welcome. EIN Presswire, Everyone's Internet News Presswire™, tries to define some of the boundaries that are reasonable in today's world. Please see our Editorial Guidelines for more information.

© 1995-2023 Newsmatics Inc. All Right Reserved.